


RoHS

REV.	ECN. #	DESCRIPTION	NAME	DATE
X1	PCN2005014	依实物取消喷码	ZHOU	2020.05.20
X2	PCN2012001	修改包装数量	XJP	2020.12.14



备注:

1. 电气特性:

- 1-1. 接触额定电流: 1A
- 1-2. 接触电阻: 100毫欧最大(插拔前后)
- 1-3. 耐压: 500V AC/1分钟.
- 1-4. 绝缘电阻: 1000兆欧最小, 测试后1000兆欧最小

2. 机械特性:

插入力: 初始 10N MAX ;
拔出: 初始 10NMAX.

3. 寿命插拔: 5000次

4. 共面度0.10mm Max (IR后)

5. 满足回流焊的无铅工艺

6. 产品必需符合RoHS要求

7. ▼符号为重点尺寸.




6	滑块	201040021	UL94V-0 颜色: 黑色	1PCS	MILLIMETERS	INCH
5	弹簧	304000073	焊镍30u"min	1PCS	X.° ±2°	X.° ±2°
4	挂钩	304000074	焊镍30u"min	1PCS	.X ±0.30	.X ±0.012
3	端子	202001090	C5210-BH, 接触区镀金2u"min; 焊接区镀锡80u"min, 全区镍底80~130u"	1PCS	.XX ±0.20	.XX ±0.008
2	铁壳	203000381	SUS301-H, 接触区镀金2u", 焊接区镀金G/F, 全区镍底30u"min	1PCS	.XXX ±0.10	.XXX ±0.004
1	MD胶芯	205560081	LCP UL94V-0 颜色: 黑色	1PCS	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO., LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO., LTD	
NO	品名	料号	规格	数量		



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	Micro SD Push Normal Type Connector (H=1.50mm) 客户图		DR		
PART NO.	102583332-D		CHKD		
PRO J.	PAGE	1/3	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.	TF010-022客户图

RoHS



PCB PATTERN LAYOUT
(GENERAL TOLERANCE:±0.05)




OPENING/CLOSE OF SWITCH



	CARD DETECT SWITCH	
CARD UNINSERTION	OPEN	
CARD HALF INERTION	OPEN	
CARD INSERTION	CLOSE	
N/O	OPEN 	CLOSE

P6	Micro-SD_VSS			MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD						
P5	Micro-SD_CLK	P11	Cover_GND	X. ° ±2°	X. ° ±2°							
P4	Micro-SD_VDD	P10	Micro-SD_GND	.X ±0.30	.X ±0.012							
P3	Micro-SD_CMD	P9	Micro-SD_CD	.XX ±0.20	.XX ±0.008							
P2	Micro-SD_CD/DATA3	P8	Micro-SD_DAT1	.XXX ±0.10	.XXX ±0.004	TITLE	Micro SD Push Normal Type Connector (H=1.50mm) 客户图	DR				
P1	Micro-SD_DATA2	P7	Micro-SD_DAT0	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO., LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO., LTD		PART NO.	102583332-D	CHKD				
Pin Define						PRO J.	PAGE	2/3	UNITS	mm	APPD	
							SIZE	A4	SCALE	1:1	DIS NO.	TF010-022客户图


RoHS



Direction of use




The bottom and top of the carton
Pad it with a piece of pearl cotton



Part Number	Description	Quantity
303020124	Carrierband (Lucent, PS W=24 PH=12,T=0.30)	24.60M*10
303040062	Box (K=K, T=7.0, 350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070025	Self-adhesive (W=21.30)	24.60M*10
303110001	Beam (K=K, T=7.0, 95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180020	REEL (BLUE, 13Inches*24mm, Ø330)	10PCS

NOTES:

- 1:Packing quantity per plate:1200PCS/Plate
- 2:Loading and packing method



- 3: Total packaging:12000PCS/Box

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X. °	±2°	X. °	±2°				
.X	±0.30	.X	±0.012	TITLE		Micro SD Push Normal Type Connector (H=1.50mm) 客户图	DR
.XX	±0.20	.XX	±0.008	PART NO.		102583332-D	CHKD
.XXX	±0.10	.XXX	±0.004	PRO J.		PAGE 3/3 UNITS mm APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO., LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO., LTD				SIZE		A4 SCALE 1:1 DIS NO.	TF010-022客户图
							