





- NOTES:
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
 3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
 4. MATERIAL: BLACK ANTI-STATIC POLYSTYRENE.
 5. THICKNESS: 0.35 ± 0.05 mm.
 6. PACKING LENGTH PER 13" REEL : 18.60METERS.
 7. COMPONENT LOAD PER 13" REEL : 1500PCS
 8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~100gf).



CKTS	30 ± 0.10	W	W1	F	50 ± 0.10
4	11.30	$24 \pm 0.3/-0$	24.4	11.5 ± 0.10	单边孔
5	12.30				
6	13.30				
7	14.30				
8	15.30				
9	16.30				
10	17.30	32 ± 0.30	32.4	14.2 ± 0.10	28.4
11	18.30				
12	19.30				
13	20.30				
14	21.30				
15	22.30				
16	23.30				
17	24.30				
18	25.30				
19	26.30				
20	27.30				
21	28.30				
22	29.30				
23	30.30				
24	31.30				
25	32.30				
26	33.30				
27	34.30	56 ± 0.30	56.4	26.2 ± 0.15	52.4
28	35.30				
29	36.30				
30	37.30				

CLASSIFICATION DIMENSION (尺寸类别): FAI (首次检验): ☒ To ☐ ☒ "MARK IS MAJOR DIM (重点尺寸标示) ☐ "MARK IS CRITICAL DIM (Cpk&Cp标示)		 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
Tolerance Unspecified (未注公差) 0.0 ± 0.10 0° $\pm 3^\circ$ 0.00 ± 0.05 0° 0 $\pm 2^\circ$ 0.000 ± 0.02 0° 00 $\pm 1^\circ$		Product Name (产品名称): 1.0Pitch H=2.5 FPC 拉拔卧式K型. 载带	
Size (图幅): A4 Unit (单位): MM Scale (比例): 1 : 1		Product No (产品料号): EB-740XXX290-00	
Project View (投影视角) 		Drawing No (图面编号): DNE00015-1	Date (日期): 2011/04/09
Page (页数): 10 OF 10 Rev (版本): 1.0		Designer (设计): Allan 04/09'11	Checked (审核): Approved (核准):