



1	2	3	4	5	6	7
RoHS			REV.	ECN.#	DESCRIPTION	NAME DATE
A			A0		NEW RELEASE	PMS 2020.07.12
B			A1		Change the packing	liuhongping 2023.01.02
C			A2		修正底视图	liuhongping 2024.07.22





NOTE:


1. Material & Finish See Table;
2. Circuit Diagram For Switch



3. Characteristic:
 - 3-1. Current Rating :1A max.
 - 3-2. Contact Resistance: 50mOhms max
 - 3-3. Insulation Resistance: 100MOhms min./500VDC
 - 3-4. Dielectric Withstanding Voltage: 500VAC/1minute
 - 3-5. Mating Force: 10N Max, Withdrawal Force: 1N Min.;
 - 3-6. Durability: 1500 Cycles
 - 3-7. Operating Temperature: -40°C to +85°C



PIN 1#	C1: VCC
PIN 2#	C5: Grand
PIN 3#	C2: Reset
PIN 4#	C6: VPP
PIN 5#	C3: Clock
PIN 6#	C7: I/O



Recommended PCB Layout

Tolerance: ± 0.05


6	Shell	SUS 304	G/F Plated On Solder Area 30μ Nickel Under Plated Overall.
5	Lever	SUS 301	/
4	Cam	SUS 301	/
3	Housing	LCP	Black,UL94V-0
2	Detect	C5191	G/F Plated on Solder Tails and Contact Area; 30μ Nickel Under Plated Overall.
1	Terminal	C5191	G/F Plated on Solder Tails and Contact Area; 30μ Nickel Under Plated Overall.
Item	Part Name	Material	Description



东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd


TITLE	1.5H Nano SIM Card CONN With Detect	DR	
PART NO.	402013622	CHKD	
PRO J.	1/2	UNITS mm	APPD
SIZE	A4	SCALE 1:1	DIS NO.

USER DIRECTION OF UNREELING



NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH




3. QUANTITY: 8000PCS/CARTON

COVER TAPE PEELING ANGLE:165°~180°


PEELING FORCE:20~130g

CARRIER TAPE

USER DIRECTION OF UNREELING



DETAIL B



MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司		
X. ±2'	X. ±2'	 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd		
.X ±0.30	.X ±0.012			
.XX ±0.20	.XX ±0.008			
.XXX ±0.10	.XXX ±0.004			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				
PART NO.	402013622	CHKD		
PRO J.	PAGE 2/2 UNITS mm	APPD		
	SIZE A4	SCALE 1:1	DIS NO.	