








■ Specification

- Voltage Rating : 30V AC/DC
- Current Rating : 0.5A AC/DC
- Withstanding Voltage : 200V AC /minute
- Insulation Resistance : $\geq 100M\Omega$ min
- Temperature Range : -40°C to $+105^{\circ}\text{C}$
- Contact Resistance : $\leq 20m\Omega$
- After Environmental Testing: $\leq 40m\Omega$
- Suitable Wire/Cable:AWG #28 to #30,OD:0.8mm max

■ Ordering Information

E1201 W V S - XX X - XX XX XX
1 2 3 4 5 6 7 8 9

- 1.A0801:Series No.
- 2.Category:W-Wafer
- 3.Soldering PCB Angle:V-Vertical angle,180°
- 4.Soldering method:S-SMD/SMT,Surface Mount Technology
- 5.Number of rows&pins:XX
- 6.Plug the pin & Special No.:Blank-Ordinary
- 7.Material(Insulators);LP-LCP,UL94V-0
- 8.Color:Blank-Natural;BK-Black
- 9.Environmental protection Standard:Blank-Ordinary
RoHS;HF-Halogen Free
- 10.Material(Pin):PB-Phosphor Bronze
- 11.Plating :SN-Bright Tin Plated;SM-Matte Tin Plated;AU-Gold flash;AU3-Gold 3U"
- 12.Package:Blank-Tape&Reel,SPQ:2K/reel preferred

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	0.80	1.90	3.78	12	8.80	9.90	11.78
03	1.60	2.70	4.58	13	9.60	10.70	12.58
04	2.40	3.50	5.38	14	10.40	11.50	13.38
05	3.20	4.30	6.18	15	11.20	12.30	14.18
06	4.00	5.10	6.98	16	12.00	13.10	14.98
07	4.80	5.90	7.78	17	12.80	13.90	15.78
08	5.60	6.70	8.58	18	13.60	14.70	16.58
09	6.40	7.50	9.38	19	14.40	15.50	17.38
10	7.20	8.30	10.18	20	15.20	16.30	18.18
11	8.00	9.10	10.98				

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

RoHS
Compliant
2013/95/EC



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
-----------	------------------------------	-----------------	------------

一般公差 GENERAL TOLERANCE	2020.03.21
.X	± 0.35
.XX	± 0.25
.XXX	± 0.10
ANGLES	$\pm 1^{\circ}$

制图 (DR):	Jerry	品名 (TITLE):	0.8mm(.031") pitch PCB Header/ Wafer R/A SMD/SMT
审核 (CHKD):		料号 (PART NO.):	A0801WVS-XX-LPHF-PBAU
版本 (REV)	A	比例 (SCALE)	1:1
核准 (APPD):	Tong	单位 (UNITS)	mm
	2020.03.21	张数 (SHEET)	1 OF 1
		图幅 (SIZE)	A4