













1. Rating: DC 30V 0.1A
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$ DC500V
4. Withstand voltage: AC 300V(30Hz)/min
5. Operating force: $250\pm 50\text{g}$
6. life test: 10000 cycles
7. Operation type: Self-locking



印制线路板

PCB Layout Recommended



电路图

Circuit Diagram

DIMENSION IN mm	
TOLERANCE UNLESS OTHERWISE SPECIFIED	

.X±0.3	X.*±5°
.XX±0.2	.X.*±3°
.XXX±0.1	.XX.*±1°

厦门市辛译精密电子有限公司							
Xiamen XinYi Xyeconn Electronics Co.,Ltd							
APR.	Alex	TITLE: 精研 Key Switch					
CHK.	Jack	DWG NO. XY-TBC8080-Z-F					
DRA.	Can	PROJ.		CUSTOMER DRAWING			
		SIZE	A4	SCALE	1:1	SHEET	1/1

7	推轴	1	POM	蓝色
6	导电接触夹	2	覆合银磷铜	镀银
5	盖板	1	PC	白色
4	弹簧	1	碳素钢	
3	勾针	1	精密钢圈	
2	基座	1	PA66	黑色
1	嵌件	2	H65 T=0.3mm	镀银
序号 NO.	名称 DESCRIPTION	数量 Q'TY	材料 MATERIAL	颜色 COLOR

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd