







REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2018-05-28			



2P 结构样式

2.0卧式贴片	DIM.A-(mm)	DIM.B-(mm)
2X2P	2.0	6.0
2X3P	4.0	8.0
2X4P	6.0	10.0
2X5P	8.0	12.0
2X6P	10.0	14.0
2X7P	12.0	16.0
2X8P	14.0	18.0
2X9P	16.0	20.0
2X10P	18.0	22.0
2X11P	20.0	24.0
2X12P	22.0	26.0
2X13P	24.0	28.0
2X14P	26.0	30.0
2X15P	28.0	32.0
2X16P	30.0	34.0
2X17P	32.0	36.0
2X18P	34.0	38.0
2X19P	36.0	40.0
2X20P	38.0	42.0

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 3A AC/DC
接触电阻: ≤0.02Ω
绝缘电阻: ≥1000MΩ
耐压值: 800V AC/minute
适用基板厚度: 1.6mm

3	短端子	n PCS	材质:黄铜,电镀:镀亮锡
2	长端子	n PCS	材质:黄铜,电镀:镀亮锡
1	Housing	1 PCS	材质:LCP (UL94V-0),颜色:本色或黑色
NO.	NAME	Q'TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW :	黄彬	2018-04-22	TITLE:	针座	DRAWNAME:	HX-PHD2.0-2x4AWT
DESIGN:			SERIES:	2002AWT SERIES	DRAWNO.	
CHECK:	张伟	2018-04-22	P/N:		UNIT:	mm
APPROVED	罗小春	2018-04-22	REV. 1.00	SCALE N/A	SHEET:	1/1
CUSTOMER DRAWING						

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	