





REV.	DESCRIPTION	APPD	DATE




NOS11-S1F1-2000-A

- 1 有柱
2 无柱



- 1) MATERIAL:
HOUSING: LCP S475 UL 94V-0
CONTACT: C5191
SHELL: SUS304-H
- 2) FINISH:
CONTACT: GOLD FLASH PLATED ON CONTACT AREA;
GOLD FLASH PLATED ON SOLDER TAILS,
- 3) ELECTRICAL CHARACTERISTICS
RATING CURRENT : 0.5A MAX.
CONTACT RESISTANCE : 50 mΩ MAX
DIELECTRIC WITHSTANDING : 500V AC MIN.
INSULATION RESISTANCE: 1000 MΩ MIN.
- 4) MECHANICAL CHARACTERISTICS
MATING CYCLE : 3000 CYCLES

SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



PART NO: NOS11-S1F2-2000-A		MATERIAL:	
LOT NO:		FINSH:	
UNIT: MM		COLOR:	
SIZE: A4		DR: 刘静	
TOLERANCES: X. X=±0.35 X. XX=±0.25 X. XXX=±0.15		GENERAL ANGLE: X. X=±3.0° X. XX=±2.0°	
CHK:		DWG NO: FP-090012	
APP:		SCALE: 1:1	
SHEET: 1 OF 1		REV: A	

东莞市高钺达电子科技有限公司

NANO SIM PUSN 卡座