






RoHS

序号	品名	材质
①	A型卧式DIP型WTB胶芯 1.25 Pitch R/A Wire To Board Housing DIP (H=3, 2)	PA66 UL94V-0 本色 Natural
②	A型卧式DIP型WTB端子 1.25 Pitch R/A Wire To Board Terminal DIP (H=3, 2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating



SECTION A-A




CKT	DIM A	DIM B	DIM C
2	1.25	3.20	4.30
3	2.50	4.45	5.55
4	3.75	5.70	6.80
5	5.00	6.95	8.05
6	6.25	8.20	9.30
7	7.50	9.45	10.55
8	8.75	10.70	11.80
9	10.00	11.95	13.05
10	11.25	13.20	14.30
11	12.50	14.45	15.55
12	13.75	15.70	16.80
13	15.00	16.95	18.05
14	16.25	18.20	19.30
15	17.50	19.45	20.55
16	18.75	20.70	21.80
17	20.00	21.95	23.05
18	21.25	23.20	24.30
19	22.50	24.45	25.55
20	23.75	25.70	26.80

技术指标(Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
- 温度范围(Temperature range): -25° C~+85° C.
- 额定电压(Rated voltage): 125V, AC/DC(=等效).
- 接触电阻(Contact resistance): ≤0.02Ω.
- 绝缘电阻(Insulation resistance): ≥100MΩ

适用线路板(PCB LAYOUT)



2 PIN

3 PIN

LOCK CONFIGURATION (锁扣位置)

深圳市连盛精密连接器有限公司

OPERATION

DRAW

SCALE

FIT

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

APPROVE

SIZE

A4

X.XXX ±0.10

Angle

SHEET

1/1

±3°

DIM

TOL

PROJ.

◆

□

PART NO.

1130200045

TITLE:

1.25-NAW

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9