

RoHS

	2	3	4	5	6	7	8	9			
G	RoHS										
F											
E											
D	技术指标:										
C	<ol style="list-style-type: none"> 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。 2. 温度范围: -25° C~85° C. 3. 额定电压: 100V, AC/DC. 4. 接触电阻: ≤0.02Ω. 5. 绝缘电阻: ≥500MΩ. 6. 额定电流: 1A , AC/DC. 7. 产品料号: 										
B											
A			OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司		
		X.X	±0.30				UNIT	mm			
		X.XX	±0.20	CHECK	APPROVE		SIZE	A4			
		X.XXX	±0.10					SHEET			1/1
		Angle	±3°					PROJ.			
		DIM	TOL					TITLE:			ZH-NAWR
	REV	DATE	MODIFICATION DESCRIPTION		CHANGE	5	6	7	8	9	