




RoHS




REV.	ECN. #	DESCRIPTION	NAME	DATE
A1	ECN1711008	Remove the protruding glue on both sides of the body	SUPER	2017.11.16
A2	ECN2011001	The bullet height size increases the tolerance control	XJP	2020.11.21




SLIDE SHELL LOCK



SLIDE SHELL OPEN



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$



Notes:

Electrical Characteristics

Contact Current Rating:0.5A

Dielectric Withstanding Voltage:AC 500V

Insulation Resistance:1000M Ω MinContact Resistance:100m Ω Max

Environmental

Temperature Range: -40°C TO +85°C

Mechanical Characteristics

Mating Cycles: 5000 Insertions

Material

Insulator: High Temperature Plastic UL94V-0

Color:Black

Contact: Copper Alloy

Shell: Stainless



Plating

Contact

Underplate: Nickel 50u".

Contact Area:GOLD 15u" Over Nickel 50u".

Solder Area: GOLD FLASH Over Nickel 50u".



MICRO SD CARD

PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)


MILLIMETERS	INCH
X. ° $\pm 2^\circ$	X. ° $\pm 2^\circ$
.X ± 0.30	.X ± 0.012
.XX ± 0.20	.XX ± 0.008
.XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO.,LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO.,LTD	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	TF掀盖1.9卡座	DR		
PART NO.	102151482	CHKD		
PRO J.	PAGE	1/2	UNITS	mm
SIZE	A4	SCALE	1:1	DIS NO.
TF004-01B<客户图>				


RoHS




NOTES:

1:Packing quantity per plate:1000PCS/Plate

2:Loading and packing method



3:Total packaging:10000PCS/Box



MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X. ° ±2°	X. ° ±2°				
.X ±0.30	.X ±0.012	TITLE	TF掀盖1.9卡座	DR	
.XX ±0.20	.XX ±0.008	PART NO.	102151482	CHKD	
.XXX ±0.10	.XXX ±0.004	PRO J.	PAGE 2/2	UNITS mm	APPD
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO.,LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO.,LTD			SIZE A4	SCALE 1:1	DIS NO. TF004-01B<客户图>