




PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material:Wafer Nylon66,UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A3960WV-02A	3.96	7.92
A3960WV-03A	7.92	11.88
A3960WV-04A	11.88	15.84
A3960WV-05A	15.84	19.80
A3960WV-06A	19.80	23.76
A3960WV-07A	23.76	27.72
A3960WV-08A	27.72	31.68
A3960WV-09A	31.68	35.64
A3960WV-10A	35.64	39.60
A3960WV-11A	39.60	43.56
A3960WV-12A	43.56	47.52
A3960WV-15A	55.44	59.40

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENE RL TOLERANCE		制 图 郑 弋 2008、07、01	料 号 PART NO.		A3960WV-NA	版 本 REV. A										
			X.±0.25	X.*±2°		审 核 张 名 2008、07、03	品 名 TITLE 3.96直针座			页 次 SHEET 1/1									
											.X±0.20	.X*±1°	核 准 杨 斌 2008、07、05	客户料号 CUTM. NO.					
																.XX±0.15	.XX*±0.5°	单 位 UNITS MM	比 例 SCALE 1:1