








[illegible][illegible][illegible]

1		2	3	4	5	6	7	8	9																																																																		
G		RoHS						<table border="1"> <thead> <tr> <th>序号</th><th>品名</th><th>材质</th></tr> </thead> <tbody> <tr> <td>①</td><td>ZH1.5直针WTB胶芯</td><td>PA66 UL94V-0 米色 白色</td></tr> <tr> <td>②</td><td>ZH1.5直针WTB端子</td><td>铜合金/表面镀锡</td></tr> </tbody> </table>		序号	品名	材质	①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色	②	ZH1.5直针WTB端子	铜合金/表面镀锡																																																									
序号	品名	材质																																																																									
①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																																									
②	ZH1.5直针WTB端子	铜合金/表面镀锡																																																																									
F																																																																											
E																																																																											
D																																																																											
C																																																																											
B								<table border="1"> <thead> <tr> <th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr> </thead> <tbody> <tr><td>2</td><td>1.5</td><td>4.5</td><td>12</td><td>16.5</td><td>19.5</td></tr> <tr><td>3</td><td>3.0</td><td>6.0</td><td>13</td><td>18.0</td><td>21.0</td></tr> <tr><td>4</td><td>4.5</td><td>7.5</td><td>14</td><td>19.5</td><td>22.5</td></tr> <tr><td>5</td><td>6.0</td><td>9.0</td><td>15</td><td>21.0</td><td>24.0</td></tr> <tr><td>6</td><td>7.5</td><td>10.5</td><td>16</td><td>22.5</td><td>25.5</td></tr> <tr><td>7</td><td>9.0</td><td>12.0</td><td>17</td><td>24.0</td><td>27.0</td></tr> <tr><td>8</td><td>10.5</td><td>13.5</td><td>18</td><td>25.5</td><td>28.5</td></tr> <tr><td>9</td><td>12.0</td><td>15.0</td><td>19</td><td>27.0</td><td>30.0</td></tr> <tr><td>10</td><td>13.5</td><td>16.5</td><td>20</td><td>28.5</td><td>31.5</td></tr> <tr><td>11</td><td>15.0</td><td>18.0</td><td></td><td></td><td></td></tr> </tbody> </table>		CKT	A	B	CKT	A	B	2	1.5	4.5	12	16.5	19.5	3	3.0	6.0	13	18.0	21.0	4	4.5	7.5	14	19.5	22.5	5	6.0	9.0	15	21.0	24.0	6	7.5	10.5	16	22.5	25.5	7	9.0	12.0	17	24.0	27.0	8	10.5	13.5	18	25.5	28.5	9	12.0	15.0	19	27.0	30.0	10	13.5	16.5	20	28.5	31.5	11	15.0	18.0			
CKT	A	B	CKT	A	B																																																																						
2	1.5	4.5	12	16.5	19.5																																																																						
3	3.0	6.0	13	18.0	21.0																																																																						
4	4.5	7.5	14	19.5	22.5																																																																						
5	6.0	9.0	15	21.0	24.0																																																																						
6	7.5	10.5	16	22.5	25.5																																																																						
7	9.0	12.0	17	24.0	27.0																																																																						
8	10.5	13.5	18	25.5	28.5																																																																						
9	12.0	15.0	19	27.0	30.0																																																																						
10	13.5	16.5	20	28.5	31.5																																																																						
11	15.0	18.0																																																																									
A																																																																											
		技术指标(Technical Index): - 温度范围(Temperature range): -25° C~+85° C. - 额定电压(Rated voltage): 100V, AC. - 额定电流(Rated current): 1.0A AC, DC. - 接触电阻(Contact resistance): ≤20mΩ . - 绝缘电阻(Insulation resistance): ≥500MΩ. - 耐压值(Withstanding voltage): 500V AC/minute. - 产品料号(Product material No.):						深圳市连盛精密连接器有限公司																																																																			
								<table border="1"> <thead> <tr> <th>REV</th><th>DATE</th><th>MODIFICATION DESCRIPTION</th><th>CHANGE</th></tr> </thead> <tbody> <tr><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td></tr> <tr><td> </td><td> </td><td> </td><td> </td></tr> </tbody> </table>		REV	DATE	MODIFICATION DESCRIPTION	CHANGE																																																														
REV	DATE	MODIFICATION DESCRIPTION	CHANGE																																																																								
								<table border="1"> <thead> <tr> <th>OPERATION</th><th>DRAW</th><th>SCALE</th><th>FIT</th></tr> </thead> <tbody> <tr> <td>X.X ±0.30</td><td> </td><td>UNIT</td><td>mm</td></tr> <tr> <td>X.XX ±0.20</td><td>CHECK</td><td>SIZE</td><td>A4</td></tr> <tr> <td>X.XXX ±0.10</td><td> </td><td>SHEET</td><td>1/1</td></tr> <tr> <td>Angle ±3°</td><td>APPROVE</td><td>PROJ.</td><td> </td></tr> <tr> <td>DIM TOL</td><td> </td><td> </td><td> </td></tr> </tbody> </table>		OPERATION	DRAW	SCALE	FIT	X.X ±0.30		UNIT	mm	X.XX ±0.20	CHECK	SIZE	A4	X.XXX ±0.10		SHEET	1/1	Angle ±3°	APPROVE	PROJ.		DIM TOL																																													
OPERATION	DRAW	SCALE	FIT																																																																								
X.X ±0.30		UNIT	mm																																																																								
X.XX ±0.20	CHECK	SIZE	A4																																																																								
X.XXX ±0.10		SHEET	1/1																																																																								
Angle ±3°	APPROVE	PROJ.																																																																									
DIM TOL																																																																											
								<table border="1"> <thead> <tr> <th>PART NO.</th></tr></thead></table>	PART NO.																																																																		
PART NO.																																																																											

[illegible][illegible][illegible]

- [illegible]

[illegible]