


RoHS

CRICUIT DIAGRAM FOR CARD DETECT SWITCH



REV.

ECN. #

DESCRIPTION

NAME




DATE

A0

NEW RELEASE

GuoXuetong

08/23/23



RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05

SMT SOLDER AREA

COPPER RESTRICTED AREA

- TOUCH AREA OF CONTACT
TIPS NO ELECTRICAL FUNCTION
- NO FIRST PCB_LAYOUT
CIRCUITS IN THE AREA

Notes:

- Material:
 - Housing: High Temperature Thermoplastic
 - Terminal: Copper Alloy
 - Shell: Stainless Steel
- Plating:
 - Terminal: 50u" Ni Underplated Overall
 - G/F Plated On Contact Area
 - G/F Plated On Solder Area
 - Shell: 30u" Ni Underplated Overall
 - G/F Plated On Contact Area And Solder Area
- Technical Speciality:
 - Rated Voltage: 30V
 - Current Rating: 0.5A
 - Insulation Resistance: 1000M Ω Min.
 - Contact Resistance: 100m Ω Max.
 - Withstanding Voltage: 500V DC For 1 Minutes.
 - Operating Temperature: -40 °C~+75 °C Humidity 80% R.H Max.

PIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O
SW	Detect Switch

MILLIMETERS	INCH
X. ° $\pm 2^\circ$	X. ° $\pm 2^\circ$
.X ± 0.30	.X ± 0.012
.XX ± 0.20	.XX ± 0.008
.XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.	




东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd

TITLE	1. 24H Push-Push Nano-SIM卡座	DR		
PART NO.	102015782	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE A4	SCALE 1:1	DIS NO.	NS011-000	客户图

RoHS


Direction of use





NOTES:

1、Packing quantity per plate: 1600PCS/Plate

2、Loading and packing method



3、Total packaging: 16000PCS/Box



Part Number	Description	Quantity
303020196	Carrier band (Lucent, PET W=24 PH=20,T=0.3)	327.0m
303040009	Box (K=K,T=7.0,350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	330m
303110001	Beam (K=K, T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE, 13Inches*24mm, φ330)	10PCS
102015782	1.24H Push-Push Nano-Sim Card<NS011-000>	16000PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co., Ltd			
X. ° ±2°	X. ° ±2°				
.X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.		TITLE	1.24H Push-Push Nano-SIM卡座	DR	
		PART NUM.	102015782	CHKD	
		PRO J.	PAGE 2/2	UNITS mm	APPD
		SIZE	A4	SCALE 1:1	DIS NO. NS011-000<客户图>