





RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05 SMT SOLDER AREA

Notes:

1. Material:
Housing: High Temperature Thermoplastic
Terminal: Copper Alloy
Shell: Stainless Steel
2. Plating:
Terminal: 50u" Ni Underplated Overall
1u" Au Plated On Contact Area
1u" Au Plated On Solder Area
Shell: 30u" Ni Underplated Overall
3. Technical Speciality:
Rated Voltage: 30V
Current Rating: 0.5A
Insulation Resistance: 1000MΩ Min.
Contact Resistance: 100mΩ Max.
Withstanding Voltage: 500V DC For 1 Min.
Operating Temperature: -40℃~+75℃ Hum

PIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved
CD1	Detect Switch
CD2	Detect Switch



MILLIMETERS	INCH
$X.^\circ \pm 2^\circ$	$X.^\circ \pm 2^\circ$
$.X \pm 0.30$	$.X \pm 0.012$
$.XX \pm 0.20$	$.XX \pm 0.008$
$.XXX \pm 0.10$	$.XXX \pm 0.004$
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilaiMetal Plastic Technology Co.,Ltd	




东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

TITLE	1. 40H No-Push Micro-SIM卡座			DR		
PART NUM.	102312892			CHKD		
PRO J.	PAGE	1/2	UNITS	mm	APPD	
	SIZE	A4	SCALE	4:1	DIS NO.	MS008-000<客户图>


ROHS

Direction of use



NOTES:

- 1、Packing quantity per plate: 1200PCS/Plate
- 2、Loading and packing method



- 3、Total packaging: 13200PCS/Box

Carrier Tape

Direction of use

DETAIL B

DETAIL B

11-REEL

The bottom and top of the carton
Pad it with a piece of pearl cotton

BOX

350*350*360mm

packaging tape

label

Part Number	Description	Quantity
303020116	Carrier band (Lucent , PET W=24 PH=20,T=0.3)	270.60m
303040077	Box (K=K,T=7.0,350*350*360)	1PCS
303060001	PE Bag (T=0.08mm , 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	273.90m
303110001	Beam (K=K , T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE , 13Inches*24mm , ϕ330)	11PCS
102312892	1.40H No-Push Micro-Sim Card<MS008-000>	13200PCS

MILLIMETERS	INCH
X. ° ±2°	X. ° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.



东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co., Ltd

TITLE	1.40H No-Push Micro-SIM卡座	DR		
PART NUM.	102312892	CHKD		
PRO J.	PAGE 2/2	UNITS mm	APPD	
SIZE A4	SCALE 3:2	DIS NO.	MS008-000<客户图>	