




RoHS

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02
A1		增加平面度标识	HZP	2025.09.17




(NOTE)

1. LEAD Co-planarity : Max 0.10mm
2. No rust, contamination, damage nor deformation effecting on function
3. Switch moving area
4. Non-cumulative tolerance
5. Circuit Drawing of switch
6. VOLTAGE RATING : 500V AC
7. CONTACT RESISTANCE: 150MΩ MAX.
8. INSULATION RESISTANCE: 1000MΩ MIN./250VDC
9. REFLOW PEAK TEMP: 260°C ±5°C, 3~5 S
10. MATING CYCLES: 1500 INSERTIONS
11. Operating Environment: -40°C to 85 °C

PART No.:

CARD SERIES: 102314342
PLATING: 2: REEL
31: G/F PAKING: SERIAL NO.


Circuit Drawing of switch



【 SIM CARD PAD LAYOUT 】

【Connector Pin Assignments】

No.	Pin name	Description
①	C1	Vcc of SIM
②	C2	RST of SIM
③	C3	CLK of SIM
④	C5	GND of SIM
⑤	C6	Vpp of SIM
⑥	C7	I/O of SIM
⑦	SW	Detection Switch
⑧~⑦	GND	Shell Ground



【 SIM Card Pin Assignments 】

PIN	Name
C1	Vcc
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	Vpp
C7	I/O
C8	Reserved



MILLIMETERS	INCH
X' ±2'	X' ±2'
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBilal Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBilal Metal Plastic Technology Co.,Ltd




东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

	TITLE		1.27mm (DIP:1.4mm) Push Micro Sim		DR	
	PART NO.		102314342-B		CHKD	
	PRO J.		PAGE	1/3	UNITS	mm
THE			SIZE	A4	SCALE	1:1
			DIS NO.			

[illegible][illegible]


RoHS

USER DIRECTION OF UNREELING



NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 7000PCS/CARTON


COVER TAPE PEELING ANGLE: 165°~180°

PEELING FORCE: 20~130g

CARRIER TAPE

USER DIRECTION OF UNREELING

DETAIL B



DETAIL B

7-REEL

4-TRIANGLE PARTITION

TAPE ON

LABEL

CARTON
335*335*250 K=K

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X.* ±2*	X.* ±2*	X.* ±2*	X.* ±2*				
.X ±0.30	.X ±0.012	.X ±0.012	.X ±0.012	TITLE	1.27mm (DIP:1.4mm) Push Micro Sim	DR	
.XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008	PART NO.	102314342-B	CHKD	
.XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004	PRO J.	PAGE 3/3 UNITS mm	APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					SIZE A4	SCALE 1:1	DIS NO.