








1. 0卧式贴片	A-(mm)	B-(mm)	C-(mm)
1. 0-2P-WT	1. 00	2. 60	4. 50
1. 0-3P-WT	2. 00	3. 60	5. 50
1. 0-4P-WT	3. 00	4. 60	6. 50
1. 0-5P-WT	4. 00	5. 60	7. 50
1. 0-6P-WT	5. 00	6. 60	8. 50
1. 0-7P-WT	6. 00	7. 60	9. 50
1. 0-8P-WT	7. 00	8. 60	10. 50
1. 0-9P-WT	8. 00	9. 60	11. 50
1. 0-10P-WT	9. 00	10. 60	12. 50
1. 0-11P-WT	10. 00	11. 60	13. 50
1. 0-12P-WT	11. 00	12. 60	14. 40
1. 0-13P-WT	12. 00	13. 60	15. 50
1. 0-14P-WT	13. 00	14. 60	16. 50
1. 0-15P-WT	14. 00	15. 60	17. 50
1. 0-16P-WT	15. 00	16. 60	18. 50

技术要求

1: 外观要求

- 1-1. 插针表面光洁、无损伤、锈蚀等缺陷。
1-2. 基座表面无脏污、飞边、排气不良等缺陷。

2:电气性能:

- 2-1. 额定电流: 1.0A
2-2. 额定电压: 50V
2-3. 耐电压: 500V
2-4. 接触电阻: $\leq 20\text{m}\Omega$
2-5. 绝缘电阻: $\geq 100\text{m}\Omega$

3: 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

>20	±0.25	序号	材料名称	数量	材质	镀涂	REMARK
>10≤20	±0.2	①	卧贴针	n	磷铜	高温亮锡	GP PASS
>3≤10	±0.15	②	塑件	1	LCP	/	GP PASS
3≤	±0.1	③	焊片	2	磷铜	高温亮锡	GP PASS
尺寸范围	公差						
设计		产品名称		SH1.0-4P-卧贴-带扣			
审核							
批准							
单位: mm	 			连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			