

RoHS		2	3	4	5	6	7	8	9																																																													
								序号	品名	材质																																																												
								①	1.5- L型立式WTB胶芯	LCP UL94V-0 自然色																																																												
								②	1.5- L型立式WTB端子	铜合金/表面镀锡																																																												
								③	1.5- L型立式WTB焊片	铜合金/表面镀锡																																																												
								④	1.5- L型立式WTB吸盖	LCP UL94V-0 自然色																																																												
								<table><tr><td>CKT</td><td>DIM A</td><td>DIM B</td></tr><tr><td>2</td><td>1.50</td><td>6.00</td></tr><tr><td>3</td><td>3.00</td><td>7.50</td></tr><tr><td>4</td><td>4.50</td><td>9.00</td></tr><tr><td>5</td><td>6.00</td><td>10.50</td></tr><tr><td>6</td><td>7.50</td><td>12.00</td></tr><tr><td>7</td><td>9.00</td><td>13.50</td></tr><tr><td>8</td><td>10.50</td><td>15.00</td></tr><tr><td>9</td><td>12.00</td><td>16.50</td></tr><tr><td>10</td><td>13.50</td><td>18.00</td></tr><tr><td>11</td><td>15.00</td><td>19.50</td></tr><tr><td>12</td><td>16.50</td><td>21.00</td></tr><tr><td>13</td><td>18.00</td><td>22.50</td></tr><tr><td>14</td><td>19.50</td><td>24.00</td></tr><tr><td>15</td><td>21.00</td><td>25.50</td></tr><tr><td>16</td><td>22.50</td><td>27.00</td></tr><tr><td>17</td><td>24.00</td><td>28.50</td></tr><tr><td>18</td><td>25.50</td><td>30.00</td></tr><tr><td>19</td><td>27.00</td><td>31.50</td></tr><tr><td>20</td><td>28.50</td><td>33.00</td></tr></table>			CKT	DIM A	DIM B	2	1.50	6.00	3	3.00	7.50	4	4.50	9.00	5	6.00	10.50	6	7.50	12.00	7	9.00	13.50	8	10.50	15.00	9	12.00	16.50	10	13.50	18.00	11	15.00	19.50	12	16.50	21.00	13	18.00	22.50	14	19.50	24.00	15	21.00	25.50	16	22.50	27.00	17	24.00	28.50	18	25.50	30.00	19	27.00	31.50	20	28.50	33.00
CKT	DIM A	DIM B																																																																				
2	1.50	6.00																																																																				
3	3.00	7.50																																																																				
4	4.50	9.00																																																																				
5	6.00	10.50																																																																				
6	7.50	12.00																																																																				
7	9.00	13.50																																																																				
8	10.50	15.00																																																																				
9	12.00	16.50																																																																				
10	13.50	18.00																																																																				
11	15.00	19.50																																																																				
12	16.50	21.00																																																																				
13	18.00	22.50																																																																				
14	19.50	24.00																																																																				
15	21.00	25.50																																																																				
16	22.50	27.00																																																																				
17	24.00	28.50																																																																				
18	25.50	30.00																																																																				
19	27.00	31.50																																																																				
20	28.50	33.00																																																																				
技术指标:		1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。 2. 温度范围: -25° C~85° C. 3. 额定电压: 100V, AC/DC. 4. 接触电阻: ≤0.02Ω. 5. 绝缘电阻: ≥500MΩ. 6. 额定电流: 1A , AC/DC. 7. 产品料号:						<table><tr><td>SCALE</td><td>FIT</td><td colspan="2" rowspan="5">深圳市连盛精密连接器有限公司</td></tr><tr><td>UNIT</td><td>mm</td></tr><tr><td>SIZE</td><td>A4</td></tr><tr><td>SHEET</td><td>1/1</td></tr><tr><td>PROJ.</td><td>◆</td></tr><tr><td colspan="2">PART NO.</td><td colspan="2">1130700005</td></tr><tr><td colspan="2">TITLE:</td><td colspan="2">ZH-NAWV</td></tr></table>			SCALE	FIT	深圳市连盛精密连接器有限公司		UNIT	mm	SIZE	A4	SHEET	1/1	PROJ.	◆	PART NO.		1130700005		TITLE:		ZH-NAWV																																									
SCALE	FIT	深圳市连盛精密连接器有限公司																																																																				
UNIT	mm																																																																					
SIZE	A4																																																																					
SHEET	1/1																																																																					
PROJ.	◆																																																																					
PART NO.		1130700005																																																																				
TITLE:		ZH-NAWV																																																																				
REV		DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT																																																														
1		2	3	4	5	6	7	8	9																																																													

[illegible][illegible][illegible]