








1 2 3 4 5 6 7 8 9 10



of uctants	Dimension						
	A	B	C	D	E	F	
11	5.50	2.40	3.00	3.63	4.95	3.60	
13	6.10	3.00	3.60	4.23	5.55	4.20	
15	6.70	3.60	4.20	4.83	6.15	4.80	
17	7.30	4.20	4.80	5.43	6.75	5.40	
19	7.90	4.80	5.40	6.03	7.35	6.00	
21	8.50	5.40	6.00	6.63	7.95	6.60	
23	9.10	6.00	6.60	7.23	8.55	7.20	
25	9.70	6.60	7.20	7.83	9.15	7.80	
31	11.50	8.40	9.00	9.63	10.95	9.60	
33	12.10	9.00	9.60	10.23	11.55	10.20	
35	12.70	9.60	10.20	10.83	12.15	10.80	
39	13.90	10.80	11.40	12.03	13.35	12.00	
41	14.50	11.40	12.00	12.63	13.95	12.60	
45	15.70	12.60	13.20	13.83	15.15	13.80	
51	17.50	14.40	15.00	15.63	16.95	15.60	Long Cover type

Note:

1. Material

- 1.1: Housing: LCP UL94-V0 Color: White
 - 1.2: Actuator: LCP OR PA UL94-V0 Color:Black.
 - 1.3: Contact: Phosphor Bronze.
 - 1.4: IFG: Phosphor Bronze.


2. Plating

- 2.1: Contact: See Part Number.
2.2: LEG: Matte Tin Plating Over Nickel

3. Rating:

- 3.1: Operating Voltage: 30V AC/DC.
 - 3.2: Current Rating: 0.2A AC/DC.
 - 3.3: Operating Temperature: -55°C~+85°C.

4. Pater Number




				版公差(VERALLAGE)		核准: LiWEI		產品料號: FPCU309-XXRL-TAG		
				X.X : ±0.30	X.X* : ±5°	CHECK: LiWEI	DATE	SCALE	UNIT	PAGE
B	底部隔栏加胶0.13mm	-----	iu	23/10'10						
REV	DESCRIPTION	ECN.NO	SL	DATE	X.XX : ±0.20	X.XX* : ±2°	DRAW: WANGHAO	20130618	1:1	mm
4	5	6	7	8	9	10				

1 2 3 4 5 6 7 8 9 10




EMBOSSING TAPE PACKING

FPC 0.3Pitch 1.0H ZIF R/A Double Contact
Connector SMT Type

PULL OUT DIRECTION




SCALE 1:4



本产品需符合 RoHS SONY00259 HF 其他
※禁止使用本公司所禁用有毒物质

NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
2. Carrier camber is within 1mm in 100mm.
3. Material: black conductive polystyrene alloy.
4. Material Thickness: 0.3 ± 0.05 mm.
5. All dimensions meet EIA-481-B requirements.
6. 5000pcs per Reel.
7. For tape width(dim W)12,16 and 24mm pilot holes are provided on one side.
For tape width(dim W)32, 44mm pilot holes are provided on both sides.



PIN NO.	W	A	B	C	PCS / REEL	REEL / CARTON	SUM(PCS)
9PIN~25PIN	16	20.5	7.50	-	4000	15	60000
31PIN~45PIN	24	28.5	11.5	-	4000	10	40000
51PIN	32	36.5	14.2	28.4	4000	8	32000

LXW 连兴旺电子(深圳)有限公司
LWXCONN ELECTRONICS (SHENZHEN) CO., LTD

TITLE: 0.3Pitch 1.0H
品名: ZIF/前插后掀式

一般公差 (TOLERANCE)		APPD: ZHONGJIAN	DWG NO: FPC0309-xxRL-TAG
X.X : ±0.30	X.X* : ±5°	核准: LiWEI	產品料號:
X.XX : ±0.20	X.XXX* : ±2°	DRAW: WANGHAO	DATE
			20130618 1:1 mm 1/1