







RoHS



With Cover



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: -25° C~85° C.
3. 额定电压: 100V, AC/DC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥500MΩ.
6. 额定电流: 1A , AC/DC.
7. 产品料号:

序号

品名

材质

①

1. 5- L型立式WTB胶芯

LCP UL94V-0 自然色

②

1. 5- L型立式WTB端子

铜合金/表面镀锡

③

1. 5- L型立式WTB焊片

铜合金/表面镀锡

④

1. 5- L型立式WTB吸盖

LCP UL94V-0 自然色

CKT	DIM A	DIM B
2	1. 50	6. 00
3	3. 00	7. 50
4	4. 50	9. 00
5	6. 00	10. 50
6	7. 50	12. 00
7	9. 00	13. 50
8	10. 50	15. 00
9	12. 00	16. 50
10	13. 50	18. 00
11	15. 00	19. 50
12	16. 50	21. 00
13	18. 00	22. 50
14	19. 50	24. 00
15	21. 00	25. 50
16	22. 50	27. 00
17	24. 00	28. 50
18	25. 50	30. 00
19	27. 00	31. 50
20	28. 50	33. 00

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X

±0.30

CHECK

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

APPROVE

DIM

TOL

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

PART NO.

1130700047

TITLE:

ZH-NAWV

1

2

3

4

5

6

7

8

9