


[illegible]

序号	品名	材质
①	1.5- L型卧式WTB胶芯	LCP UL94V-0 自然色
②	1.5- L型卧式WTB端子	铜合金/表面镀锡
③	1.5- L型卧式WTB焊片	铜合金/表面镀锡




SECTION A-A

CKT	DIM A	DIM B	CKT	DIM A	DIM B
2	1.50	6.00	12	16.50	21.00
3	3.00	7.50	13	18.00	22.50
4	4.50	9.00	14	19.50	24.00
5	6.00	10.50	15	21.00	25.50
6	7.50	12.00	16	22.50	27.00
7	9.00	13.50	17	24.00	28.50
8	10.50	15.00	18	25.50	30.00
9	12.00	16.50	19	27.00	31.50
10	13.50	18.00	20	28.50	33.00
11	15.00	19.50			

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 100V, AC/DC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A , AC/DC.
7. 产品料号:



				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130700066
				X.XXX	±0.10				SHEET	1/1		
				Angle	±3°	APPROVE			PROJ.		TITLE:	ZH-AWR
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	DIM		TOL					