

Features:

- 1. 2~24 circuits available;
- 2. Contact: Brass;
- 3. Material: PA66 UL94V-0 or UL94V-2;
- 4. Finished: Tin-plated;
- 5. Mates with H420012 Housing;
- 6. Color: Black/Natural(Clear)/Ivory;




Specification:

Current Rating: 7A AC/DC
Voltage rating: 600V AC(RMS) or 600V DC Max
Contact resistance: 15mΩ Max
Insulation resistance: 1000MΩ Min
Dielectric withstanding voltage: 1500V AC/minute
Ambient temperature rang: -25℃~85℃


Dimensional Information(mm)

Circuits	DIM A	DIM B	Circuits	DIM A	DIM B
02	4.20	5.60	14	25.20	30.80
04		9.80	16	29.40	35.00
06	8.40	14.00	18	33.60	39.20
08	12.60	18.20	20	37.80	43.40
10	16.80	22.40	22	42.00	47.60
12	21.00	26.60	24	46.20	51.80

SERIES NO: H420013-XX-XX
PIN Q' PY: 02~24
Color:
CB: Black
CN: Natural(Clear)
CI: Ivory



P C B LAYOUT



REV	Description	DATE	GENERAL TOLERANCES (unless specified)	UNITS	MM	DATE	2012-03-05	 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
			X.X±0.4	SCALE	1:1	DRAWING	Liu zhi guo		
			X.XX±0.25	REV	A	CHECKED BY	Li peng	PRODUCT NAME	4.2 mm vertical header
			X.XXX±0.15			APPROVAL BY		RART NUMBER	H420013-XX-XX