










SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer PA46, UL94V-0
PIN Brass Tin-plated



编 号	尺寸 (mm)	
	A	B
A2004-2X02A	2.00	6.00
A2004-2X03A	4.00	8.00
A2004-2X04A	6.00	10.00
A2004-2X05A	8.00	12.00
A2004-2X06A	10.00	14.00
A2004-2X07A	12.00	16.00
A2004-2X08A	14.00	18.00
A2004-2X09A	16.00	20.00
A2004-2X10A	18.00	22.00
A2004-2X11A	20.00	24.00
A2004-2X12A	22.00	26.00
A2004-2X20A	38.00	42.00

GENEERL TOLERANCE

X±0.25	X'±2°
.XX±0.20	.X'±1°
.XXX±0.15	.XX'±0.5°
.XXX±0.10	.XXX'±0.5°

制 图	审 核	核 准	单 位
DRAWING	CHECK	APPROVAL	UNITS

料 号	版 本
PART NO.	REV.
品 名	页 次
TITLE	SHEET
客户料号	
CUTM. NO.	

A2004-2XnA	A
PHD直针	1/1
WAFER DIP TYPE	