

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:30mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c

Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Resistance To Soldering Heat:

245°C±5°C, 10s(PBT insulator)

Dimension antitheses list	
ITEM	A
Standard	2.90



Ordering Information

HC-CZ 254 - * - N - W - * - ** - *		No. of Rows	No. of Pins	Type	Length (Plastic)	Contact Plating	Contact Type
		2= Dual Row	10/16/20Pin	W= Wire	100.00	G0: Gold Flash	F= Female
		3= Three Row	32/44/48Pin			G1: 1u" Gold	M= male
		4= Four Row	64Pin			G2: 3u" Gold	
						G3: 5u" Gold	
						G4: 10u" Gold	
						G5: 15u" Gold	
						G6: 30u" Gold	
						S0: Gold Flash/Tin	
						S1: Tin	



深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO., LTD

产品名称 TITLE	欧式插座2.54 双排 弯公座	版本 REV.	A
产品料号 PART NO.	HC-CZ254-2-N-W-13.0-XX-M	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL				
			X.XX ±0.20	比例 SCALE				
			X.XXX ±0.10	投影 Projection				
			Angle ±3.0°					
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						