




适应基板厚度: 1.2mm—1.6mm
温度范围: -25C° —85C°
额定电压: 250V AC/DC
额定电流: 3A
接触电阻: ≤0.01Ω
绝缘电阻: ≥1000MΩ
耐压: 1000V AC/minute

型号 Type	尺寸Dimensions mm	
	A	A
2P	7.5	2.5
3P	10	5.0
4P	12.5	7.5
5P	15	10.0
6P	17.5	12.5
7P	20	15.0
8P	22.5	17.5
9P	25	20.0
10P	27.5	22.5
11P	30	25.0
12P	32.5	27.5
13P	35	30.0
14P	37.5	32.5
15P	40	35.0



技术要求:

- 1) 材质: 见附表.
- 2) 电镀: 见附表.
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象.
- 4) 端子表面无氧化、电镀不良等现象.

2	PIN	材质: 黄铜, 电镀: 亮锡60u"MIN
1	Housing	材质: PA66 (UL94V-0), 颜色: 本色
NO.	Draw Name	XH-XXA

一般公差
TOLERANCES
X. ±0.15 .XX±0.05
.X±0.1 .XXX±0.02
ANGLES ±1°

品名: 2.5XH立式		制图
材料: PA66		审核
比例: 1:1		批准
单位: mm	时间: 2021.06.08	

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD