

RoHS

	2	3	4	5	6	7	8	9		
G										
F										
E										
D			SECTION A-A							
C										
B										
A			<p>技术指标:</p> <ol style="list-style-type: none"> 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。 温度范围: -25° C~85° C. 额定电压: 100V, AC/DC. 接触电阻: ≤0.02Ω. 绝缘电阻: ≥500MΩ. 额定电流: 1A , AC/DC. 产品料号: 							
			OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司 PART NO. TITLE: ZH-NAWR	
			X.X	±0.30	CHECK APPROVE	A4	UNIT	mm		
			X.XX	±0.20			SIZE	A4		1130700061
			X.XXX	±0.10			SHEET	1/1		
			Angle	±3°			PROJ.			
			DIM	TOL						
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	5	6	7	8	9	