





适应基板厚度: 1.2mm—1.6mm
温度范围: -25C° —85C°
额定电压: 250V AC/DC
额定电流: 3A
接触电阻: ≤0.01Ω
绝缘电阻: ≥1000MΩ
耐压: 1000V AC/minute



技术要求:

- 1) 材质: 见附表.
- 2) 电镀: 见附表.
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象.
- 4) 端子表面无氧化、电镀不良等现象.

型号 Type	尺寸Dimensions mm	
	A	B
2P	7.5	2.5
3P	10	2.5
4P	12.5	3.86
5P	15	6.36
6P	17.5	8.86
7P	20	11.36
8P	22.5	13.86
9P	25	16.36
10P	27.5	18.86
11P	30	21.36
12P	32.5	23.86
13P	35	26.36
14P	37.5	28.86
15P	40	31.36

2	PIN	材质: 黄铜, 电镀: 亮锡60u"MIN
1	Housing	材质: PA66 (UL94V-0), 颜色: 本色
NO.	Draw Name	XHB-XXA

一般公差 TOLERANCES	
X. ±0.15	.XX ±0.05
.X ±0.1	.XXX ±0.02
ANGLES ±1°	

品名: 2.5XHB立式		制图	审核
材料: PA66		批准	
比例: 1:1	单位: mm	时间: 2021.06.08	