


[illegible][illegible]

	-	2	3	4	5	6	7			8	9																																		
G	RoHS										<table><tr><td>序号</td><td>品名</td><td>材质</td></tr><tr><td>①</td><td>ZH1.5直针WTB胶芯</td><td>PA66 UL94V-0 米色 白色</td></tr><tr><td>②</td><td>ZH1.5弯针WTB端子</td><td>铜合金/表面镀锡</td></tr></table>		序号	品名	材质	①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色	②	ZH1.5弯针WTB端子	铜合金/表面镀锡																								
序号	品名	材质																																											
①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																											
②	ZH1.5弯针WTB端子	铜合金/表面镀锡																																											
F																																													
E																																													
D																																													
C	技术指标(Technical Index)： 1.温度范围(Temperature range)：-25° C~+85° C. 2.额定电压(Rated voltage)：100V，AC。 3.额定电流(Rated current)：1.0A AC,DC。 4.接触电阻(Contact resistance)：≤20mΩ 。 5.绝缘电阻(Insulation resistance)：≥500MΩ。 6.耐压值(Withstanding voltage)：500V AC/minute。 7.产品料号(Product material No.)：																																												
B																																													
A	<table><tr><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td rowspan="2">SCALE</td><td rowspan="2">FIT</td><td colspan="2" rowspan="5">深圳市连盛精密连接器有限公司</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td>UNIT</td><td>mm</td></tr><tr><td>X.XXX</td><td>±0.10</td><td>SIZE</td><td>A4</td></tr><tr><td>Angle</td><td>±3'</td><td rowspan="2">APPROVE</td><td>SHEET</td><td>1/1</td><td>PART NO.</td><td>1130700030</td></tr><tr><td>REV</td><td>DATE</td><td>MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>DIM</td><td>TOL</td><td>TITLE:</td><td>ZH-AWA</td></tr></table>										OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	X.XXX	±0.10	SIZE	A4	Angle	±3'	APPROVE	SHEET	1/1	PART NO.	1130700030	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	TITLE:	ZH-AWA		
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																								
X.X	±0.30																																												
X.XX	±0.20	CHECK	UNIT	mm																																									
X.XXX	±0.10		SIZE	A4																																									
Angle	±3'	APPROVE	SHEET	1/1			PART NO.	1130700030																																					
REV	DATE		MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	TITLE:	ZH-AWA																																					
	1	2	3	4	5	6	7	8	9																																				

[illegible]

- [illegible]

[illegible][illegible][illegible]