




适应基板厚度: 1.2mm—1.6mm
温度范围: -25℃—85℃
额定电压: 250V AC/DC
额定电流: 2A
接触电阻: $\leq 0.01\Omega$
绝缘电阻: $\geq 100M\Omega$
耐压: 800V AC/minute

型号 Type	尺寸Dimensions mm	
	A	B
2P	6.0	2.0
3P	8.0	4.0
4P	10.0	6.0
5P	12.0	8.0
6P	14.0	10.0
7P	16.0	12.0
8P	18.0	14.0
9P	20.0	16.0
10P	22.0	18.0
11P	24.0	20.0
12P	26.0	22.0
13P	28.0	24.0
14P	30.0	26.0
15P	32.0	28.0



技术要求:

- 1) 材質: 見附表。
- 2) 電鍍: 見附表。
- 3) 鑄件表面平整、光潔、无毛刺、气泡、燒焦、變形、澇口无拉伤、多料或缺料等不良現象。
- 4) 端子表面无氧化、電鍍不良等現象。

[illegible]