



印制线路板
PCB Layout Recommended

7	推轴	1	POM	白色
6	盖板	1	PC	灰色
5	弹簧	1	碳素钢	
4	勾针	1	精密钢圈	
3	导电接触夹	2	覆合银磷铜	镀银
2	嵌件	2	H65 Y=0.35mm PPA	镀银
1	基座	1	PA66	黑色
序号 NO.	名称 DESCRIPTION	数量 Q'TY	材料 MATERIAL	颜色 COLOR

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 精密 Key Switch	
.XX±0.2	.X.*± 3°	CHK.	Jack	DWG NO. XY-TBC8585-W-F	
.XXX±0.1	.XX.*± 1°	DRA.	Can	PROJ. CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A

1. Rating:DC 30V 0.1A
2. Contact resistance:≤100mΩ
3. Insulation resistance:≥100MΩ DC500V
4. Withstand voltage:AC 300V(30Hz)/min
5. Operating force:250±50g
6. life test:10000 cycles
7. Operation type: Self-locking