

RoHS

1.50±0.1(PITCH)

DIMA±0.20

DIMB±0.25

A

A

0.50±0.05

3.65±0.25

2.3±0.2

4.70±0.25

2.9±0.2

TYPE 1 (无K脚)

0.7±0.2

TYPE 2 (打K脚)

(2.9)

(3.5)

SECTION A-A

序号

品名

材质

①

ZH1.5直针WTB胶芯

PA66 UL94V-0 米色
白色

②

ZH1.5直针WTB端子

铜合金/表面镀锡

CTK

A

B

CTK

A

B

2

1.5

4.5

12

16.5

19.5

3

3.0

6.0

13

18.0

21.0

4

4.5

7.5

14

19.5

22.5

5

6.0

9.0

15

21.0

24.0

6

7.5

10.5

16

22.5

25.5

7

9.0

12.0

17

24.0

27.0

8

10.5

13.5

18

25.5

28.5

9

12.0

15.0

19

27.0

30.0

10

13.5

16.5

20

28.5

31.5

11

15.0

18.0

技术指标(Technical Index):

1. 温度范围(Temperature range): -25° C~+85° C.

2. 额定电压(Rated voltage): 100V, AC.

3. 额定电流(Rated current): 1.0A AC, DC.

4. 接触电阻(Contact resistance): ≤20mΩ .

5. 绝缘电阻(Insulation resistance): ≥500MΩ.

6. 耐压值(Withstanding voltage): 500V AC/minute.

7. 产品料号(Product material No.):

DIMA±0.1

1.50±0.1

Ø0.70±0.05

适用线路板(PCB LAYOUT)

OPERATION

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

DRAW

CHECK

APPROVE

SCALE

UNIT

SIZE

SHEET

PROJ.

FIT

mm

A4

1/1

深圳市连盛精密连接器有限公司

PART NO.

1130700021

TITLE:

ZH-NA

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9