






1:SPECIFICATION:

- 1.1 Voltage Rating: 60V AC/DC
- 1.2 Rated current : For signal pin 0.3 AMPS/Pin
For power pin 12 AMPS Max/(All Power Pin)
- 1.3 Temperature Range: -40 °C to +85°C
- 1.4 Contact Resistance:
Signalpin:Initial:50mΩ MAX
AFTER TEST:Δ20mΩ
Power pin:Initial:15mΩ MAX
AFTER TEST:15mΩ MAX
- 1.5 Insulation Resistance
Initial: 500 MΩ Minimum.
After test: 500 MΩ Minimum.
- 1.6 Dielectric Withstanding Voltage
NO EVIDENCE OF BREAKDOWN IN AC 100 V,1 MINUTE
- 1.7 MATING—UNMATING FORCE:
MATING FORCE: 1 CYCLE: 40N MAX
30 CYCLE:40N MAX
UNMATING FORCE: 1 CYCLE: 10N MIN
30 CYCLE: 8N MIN
- 1.8 SALT WATER SPRAY: TEMPERATURE 35°C±2°C
DENSITY OF SALT WATER 5±1%
DURATION:48±2 HOUR
Storage Temperature Range -40°C to +85°C
0 to 90 % RH (Relative humidity).





4	POWER CONTACT-B	COPPER ALLOY, Adu* Min ON CONTACT AREA, Adu* Min ON SOLDER AREA, Ni 50u*Min ALL OVER			
3	POWER CONTACT-A	COPPER ALLOY, Adu* Min ON CONTACT AREA, Adu* Min ON SOLDER AREA, Ni 50u*Min ALL OVER	7	REEL	PLASTIC
2	SIGNAL CONTACT	COPPER ALLOY, Adu* Min ON CONTACT AREA, Adu* Min ON SOLDER AREA, Ni 50u*Min ALL OVER	6	COVER TAPE	FLYESTER
1	HOUSING	LCP, BLACK, UL 94 V-0	5	EMBOSSED CARRIER TAPE	PS
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS




深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2° X.X ±0.5°				0.3PH 单槽BTB 公座68+6P	
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW59M-BTB2X34-6-049B
		马跃	2014-02-23	MOLD NO.	
		APPROVED BY:	DATE :	DRAW NO:	HYC-2511201534
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1



STYLE AND DIMENSION OF REEL

PER REEL 15000 CONNECTORS



 深圳市华宇创精密电子有限公司					
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2" X.*' ±0.5"  UNIT: mm [inch] SCALE: 1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图		
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.		
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.		
			DRAW NO:		
		SHEET NO.	1 OF 1		