


Ordering Information
B256-1 XX A0 B S B E 9


30u" MIN NICKEL UNDERPLATING OVER ALL

Temperture Range: -40°C to $+105^{\circ}\text{C}$



2.00XNo. of Positions+6.2±0.25

2.00XNo. of Positions+7.3±0.25



NQ OF PINS	Contact	Plating	INSULATOR	Back	PACKING
4-100P	Full Contact Gold	Semi-gold	MATERIAL:	G Grey427	A PE Bag
	A0=0.8u"	B0=0.8U'	B PA6T	E Grey413	B Tape & Feet
	A1=1u"	B1=1U'	C PA9T	W White	C Tube
	A2=1.5u"	B2=1.5U'	D LCP	U Blue	D Tube+CAP
	A3=2u"	B3=2U'			E Tray
	A4=3u"	B4=3U'			
	A5=5u"	B5=5U'			
	A6=10u"	B6=10U'			
	A7=15u"	B7=15U'			
	A8=20u"	B8=20U'			
	A9=30u"	B9=30U'			
	S1=Quinary Tinned				
	S2=Matte Tinned				
	S3=Tinned plated High temperature				

						OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
						X.X	+0.25	UNIT		MM				
						X.XX	+0.20	SIZE	A4	DESIGN	李官淼2022.07.07	PART NO	B256-1XXA0BSBE9	
						X.XXX	+0.10							
						Angle	+13°	SHEET	1/1	CHECK		TITLE	BH2.0*5.6 XXP DIP:2.8 两端带窗口 SMT 镀普金 PA6T 黑色 盒装	
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	APPROVE	DIM	TOL	PROJ.		APPROVE		Customer No.	

Yxcon 东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co., Ltd.

李官淼2022.07.07	PART NO	B256-1XXA0BSRF9
---------------	---------	-----------------

BH2.0*5.6 XXP DIP:2.8 两端带窗口

SMT 镀普金 PA6T 黑色 盒装

Cust order	No
------------	----