

Specifications

Ordering Information

A 备注(Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u", 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

P315-12 XX A0 B S 072 C 1

HEIGHT OF HOUSING: 08: 0.8mm, 10: 1.0mm, 15: 1.5mm

NO. OF PINS PER ROW: 2-50P

Full of Gold: A0=0.8u", A1=1u", A2=1.5u", A3=2u", A4=3u", A5=5u", A6=10u", A7=15u", A8=20u", A9=30u"

Plating: Semi-gold: B0=0.8u", B1=1u", B2=1.5u", B3=2u", B4=3u", B5=5u", B6=10u", B7=15u", B8=20u", B9=30u"

INSULATOR MATERIAL: B: PA6T, C: PA9T, D: LCP

LENGTH OF TERMINAL: A: PE Bag, B: Tape & Reel, C: Tube, D: Tube+CAP, E: Tray

PACKING

B 2. 特性 (characteristics):

额定电流: 1 AMP

Raring Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.


耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C





H				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	李青杰2023.06.20	PART NO	P315-1206A0BS072C1	
				X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK		TITLE	1.27排针 2*6P L=7.2/1.8 180度 H=1.5 PA6T料 镀普金 1K/袋	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		DIM	TOL	PROJ.		APPROVE		Customer No.	