

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 8A
- 2.Withstanding voltage : AC1600V/1Min.

IEC Standard





1. Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	2.5KV	2.5KV	2.5KV
Rate voltage(V)	320V	250V	160V
Rate current(A)	7A		

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.81mm, Poles : N=02~24P
- 3.Operating temperature:-40°C~+105°C
- 4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm							
To	Over	To	Over	To	Over	To	Over	To	
6	10	10	24	30	60	100	150	150	0.1/10
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'	

5.RoHS Compliance



Ordering Information

JL15EDGA - 381

XX

X

XX


Pitch
381=3.81PH

No.of pins
2P,3P,4P~24P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Serial code
01-99

PCB LAYOUT



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		2021.4.13

DRAW	XH.LI	SCALE	FIT	JILN® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO., LTD		
		UNIT	mm			
CHECK	W.CHEN	SIZE	A4	PART NO.	JL15EDGA-381XXXXX	
APPROVE	J.CHEN	SHEET	1/1	TITLE:	JL15EDGA-3.81-XXP插拔式母座/弯脚	
		PROJ.	DATE OF ISSUE:	2021.4.13	REV:	A0