










RECOMMENDED FOOTPRINT PATTERN(TOLERANCE:±0.05)



RECOMMENDED METAL MASK LAYOUT(TOLERANCE:±0.03),T=0.12



MATED VIEW



RECOMMENDED REFLOW TEMPERATURE PROFILE USIN LEAD-FREE SOLDER PASTE


NOTES:


- 1.0 VOLTAGE: 60V AC/DC
- 2.0 IMPEDANCE: 50Ω
- 3.0 OPERATION TEMPERATURE: -40° C TO +85° C
- 4.0 CONTACT RESISTANCE: 20mΩ MAX INTIAL, 40mΩ MAX AFTER TEST
- 5.0 INSULATION RESISTANCE: 500MΩ MIN INTIAL, 100MΩ MIN AFTER TEST
- 6.0 DIELECTIC WITHSTANDING VOLTAGE: 200V AC FOR ONE MINUTE
- 7.0 DURABILITY: 30 CYCLES
- 8.0 IR REFLOW CYCLE: 2 CYCLES MAX.
- 9.0 VSWR:
 - 1.3 MAX. at 0.1~3 GHz ;
 - 1.4 MAX. at 3~6 GHz ;
 - 1.5 MAX. at 6~8 GHz ;
- 10.0 Salt spray: 48H

3	GROUND CONTACT	CR191, GOLD PLATING OVER NICKEL	6	REEL	PLASTIC
2	CONTACT	CR191, GOLD PLATING OVER NICKEL	5	COVER TAPE	PLYESTER
1	HOUSING	LCP, BLACK, UL 94 V-0	4	EMBOSSED CARRIER TAPE	PS
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS





深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RF四代板端天线座	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW27-RF2020-060B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2511251138
				SHEET NO.	1 OF 1





DIRECTION OF UNREELING



TRAILER

TAPING (FREE)

LEADER



STYLE AND DIMENSION OF REEL

PER REEL 5000 CONNECTORS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	包装图	
	CHECKED BY:	DATE :	PART NO.	
	马跃	2014-02-23	MOLD NO.	
	APPROVED BY:	DATE :	DRAW NO:	
	邱敏	2014-02-23	SHEET NO.	1 OF 1