








RoHS Compliant



元件孔位图  
从上向下插 ⊗



安装面板图  
面板内侧 ⊗



⑧	增力片	65Mn t=0.4	1	Ni	※
⑦	右插针	QSn6.5-0.1 t=0.5	1	Ag	※
⑥	中插针	QSn6.5-0.1 t=0.5	1	Au	※
⑤	3号插针	QSn6.5-0.1 t=0.5	1	Au	※
④	接地片	QSn6.5-0.1 t=0.5	1	Sn	※
③	1号2号插针	QSn6.5-0.1 t=0.5	2	Au	※
②	左插针	QSn6.5-0.1 t=0.5	1	Ag	※
①	基座	PA66 UL94HB	1	黑色	※
序号	名称	材 料	数 量	镀层/颜色	备 注

单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	品名(ITEM NO)	卡侬插座
			料号(PART NO)	MLD-XLR-11-N3B
比例(SCALE): 1:1	XX ± 0.38	模号(MODEL NO)	设计 (DESIGN)	柯南
	XXX ± 0.20		审核 (CHECKED)	邱敏
	XXXX ± 0.10	图号(DWG NO)	核准(APPROVED)	陈镇
	X ± 5°	MLD-2509031032		
	X.X ± 2°			