






NOTES:



- 1.0 VOLTAGE: 30V AC/DC
- 2.0 IMPEDANCE: 50Ω
- 3.0 POWER RATING: 2W
- 4.0 OPERATION TEMPERATURE: -40° C TO +85° C
- 5.0 CONTACT RESISTANCE: 70mΩ MAX INITIAL, 90mΩ MAX AFTER TEST
- 6.0 INSULATION RESISTANCE: 500MΩ MIN INITIAL, 100MΩ MIN AFTER TEST
- 7.0 DIELECTRIC WITHSTANDING VOLTAGE: 300V AC FOR ONE MINUTE
- 8.0 DURABILITY: 100 CYCLES
- 9.0 IR REFLOW CYCLE: 2 CYCLES MAX.
- 10.0 VSWR:
 - 1.2 MAX. at DC~3 GHz ; 1.3 MAX. at 3~6 GHz ; 1.5 MAX. at 6~11 GHz
- 11.0 INSERTION LOSS:
 - 0.1dB MAX. at DC~3 GHz ; -0.2dB MAX. at 3~6 GHz ; -0.5dB MAX. at 6~11 GHz
- 12.0 ISOLATION:
 - 20dB MIN. at DC~3 GHz ; -15dB MIN. at 3~6 GHz ; -10dB MIN. at 6~11 GHz

3	SIGNAL OUT CONTACT	STAINLESS STEEL, GOLD PLATING OVER NICKEL			
2	SIGNAL IN CONTACT	STAINLESS STEEL, GOLD PLATING OVER NICKEL			
1	HOUSING	LCP, BLACK, UL 94 V-0	4	GROUND CONTACT	COPPER ALLOY, GOLD PLATING ON SOLDER AREA, OVER NICKEL
NO.	PART NAME	DESCRIPTION , REMARKS	NO.	PART NAME	DESCRIPTION , REMARKS





深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RF三代测试座
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW23-RF2020-090B
UNIT: mm [inch]	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2511191646
SCALE: 1:1	SIZE: A4		SHEET NO. 1 OF 1



DIRECTION OF UNREELING



TRAILER

TAPING (FREE)

LEADER

STYLE AND DIMENSION OF REEL

PER REEL 3000 CONNECTORS



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." ± 2 "X.X" ± 0.5 "

UNIT: mm [inch]

SCALE: 1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

CHECKED BY:

马跃

DATE :

2014-02-23

APPROVED BY:

邱敏

DATE :

2014-02-23

PART NAME:

包装图

PART NO.

MOLD NO.

DRAW NO:

SHEET NO.

1 OF 1