


Temperature Range: -40°C to $+105^{\circ}\text{C}$



HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Semi-gold	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING:
10: 1.0mm	1~40P	A0=0.8u"	B0=0.8U'	A: PA9T		A: PE Bag
15: 1.5mm		A1=1u"	B1=1U'	B: PA6T		B: Tape & Reel
20: 2.0mm		A2=1.5u"	B2=1.5U'	C: LCP		C: Tube
		A3=2u"	B3=2U'			D: Tube+CAP
		A4=3u"	B4=3U'			E: Tray
		A5=5u"	B5=5U'			
		A6=10u"	B6=10U'			
		A7=15u"	B7=15U'			
		A8=20u"	B8=20U'			
		A9=30u"	B9=30U'			
		S1=Gold plating				
		S2=Matte Tin plating				
		S3=Tin-plated High-temperature				

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE		A4	DESIGN		李官森2023.08.16	PART NO
				X.XXX	±0.10	SHEET		1/1	CHECK			TITLE
		/		Angle	±3°							2.0排针 1*20P*2 L=13.0/3.0/3.0 180度 PBT 镀1U"金 200个/袋摆整齐
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.			APPROVE			Customer No.