





SCHEMATIC



PCB LAYOUT (TOP VIEW)

SPECIFICATION

1. Rating : DC 30V 0.5A;
2. Contact resistance: $\leq 0.03\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V) ;
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-25N;
6. Life test: 5,000 cycles.

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
5	HOUSING	1	PBT	
4	BUSHING	1	BRASS	Ni-Plating
3	SPRING CONTACT	1	BERYLLIUM COPPER	Ag-Plating
2	TERMINAL	1	BRASS	Ag-Plating
1	TERMINAL	1	BRASS	Ag-Plating
UNIT: MM		TYPE:	MODEL NO:	PAPER NO: A4 PAGE 1 OF 1
		PHONE JACK	WQP-WQP518MA	TOLERANCE ANGLES SCALE VER
DESIGNER				± 0.15 $\pm 1.5^\circ$ 3:1 1
BY:	CHECK			
BY:	APPROVED			
BY:				

WENZHOU QINGPU ELECTRONICS CO., LTD