





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X9	产品新模开发, 尺寸变更, 图面升级整理图面	2025.07.08	阿树




SECTION:A-A
SCALE: 1:1



SECTION:B-B
SCALE: 1:1



SECTION:C-C
SCALE: 1:1



SECTION:D-D
SCALE: 1:1

- 规格 Specification:
- 1.Voltage rating额定电压: 250V AC/DC.
 - 2.Current Rating额定电流: 3A AC/DC.
 - 3.Withstanding Voltage耐电压: 1500V AC/Minute.
 - 4.Temperature Range温度范围: -25℃~+85℃.
 5. Contact Resistance接触电阻: 20 mΩ Max.
 - 6.Insulation Resistance绝缘电阻: 1000 MΩ Min.

PART NO.:

X9555 T-P XX-A
① ② ③ ④ ⑤

- ①Series Number.
②Category: T-terminal
③Material: P-Phosphorous bronze
④Finish:SN-Tin-plated ; G01-Gold Flash
⑤Other Types: A-Tight Type (紧端)

X9555T-PSN-A	Phosphor Bronze	AWG#22-28	Stamping Before Pating:30u"Ni;70u"Sn	X9555H-A
PART NO	Material	Wire Range	Finish	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.54mm Pitch Terminal
CHECKED		UNIT:	mm/in	PART NO.: X9555T-PSN-A
APPROVED		SIZE:	A4	DWG NO.: