





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X5	产品外观及尺寸变更，图面升级整理图面	2025.07.16	阿树





PCB Layout



常态：1-2导通 4-5导通
按下：2-3导通 5-6导通

- Specifications (规格):
- 1.Current rating (额定电流):100mA 30vDC
 - 2.Contact resistance (接触电阻): $\leq 200m\Omega$
 - 3.Insulation resistance (绝缘电阻): $\geq 100M\Omega$ Min
 - 4.Operating Force (按压力): $250\pm 50gf$
 - 5.Mating cycles (使用寿命): 10000 cycles Min

PAPT NO	XKB5858-X-TP-75
OPERATION	W:NO LOCK Z:LOCK



7	Crochet Needle	Sus	
6	Spring	Sus	
5	Contact spring	Composite silver	
4	Cover	PPA	Black
3	Guide rod	PPA	Beige
2	Terminal	H62 T=0.30mm	
1	Contact	PPA	Grey
ITEM	PAPT NAMF	MATERIAL	COLOR/NOTES

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:	MODEL TYPE: KEY SWITCH
CHECKED		UNIT: mm/in	PART NO.: XKB5858-X-TP-75
APPROVED		SIZE: A4	DWG NO.: