


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.05.22	
A2	N/A	A2X1		2025.09.05	



Specifications:

- 1.Voltage rating:250VAC/DC
250V AC/DC
- 2.Current rating:3A AC/DC
: 3A AC/DC
- 3.Withstanding voltage:500V AC/minute
500V AC/
- 4.Temperature range: -55 -+105
-55 -+105
- 5.Insulation resistance:1000MΩ MIN
1000MΩ MIN
- 6.Contact resistance:30mΩ Max
30mΩ Max

Material:



- 7.Rubber core:PBT UL94V-0
PBT UL94V-0
- 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
SPCC-SD, / /
- 9.Terminal:Copper alloy

PART NO.:

X01 XX F X X X X

Series NO.

Row No.Pin No.XX-09;15;25;37
Welding Board Angle :F-Female
T Tradutional C Car-pin
Planting Categoty: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:7AuSn'
Color:B-BLACK W-White BL-Blue
1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4



NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	16.35	24.99	30.80	19.28
15	24.75	33.30	39.20	27.65
25	38.35	47.04	53.05	41.28
37	54.75	63.50	69.40	57.71

	TYPE-1:	TYPE-2:	TYPE-3:	TYPE-4:

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X01XXFXXXX
APPROVED		SIZE: A4	DWG NO.: