

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

NOTES:
MATERIAL:

- 3.PLATING :GOLD PLATING OVER NICKEL.
4.SHIELD: COPPER ALLOY(OR STEEL ALLOY) 0.20mm THICKNESS PLATING NI.
5.LED: OPTION.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
2.CURRENT RATING :1.5 AMP.
3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
5.DIELECTRIC WITHSTANDING
RESISTANCE :1000V AC RMS 50Hz. 1MIN.
6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.

MECHANICAL:

- 1.DURRABILITY:750 CYCLES MIN.
2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO +85°C.
2. OPERATION : 0°C TO 70°C.





MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68,SUBPART F.

PART NUMBER:

52-03488421X1X11X

LED SERIES PCB JACK
LED系列PCB接口
LED (屏蔽壳) :1-W/O SHIELD (非屏蔽)
1/2 SHIELD (半包) 3-FULL SHIELD (全包)
S (插口) :1-1X1 (一口) 2-1X2 (二口)
4 (四口) 6-1X6 (六口) 8-1X8 (八口)
POSITIONS (金针位置) :8-8POSITIONS (8P)
LOGO
ACTS (金针根数) :8-8CONTACTS (8C)
TAB (边定位铁脚) :0-W/O PEG (无铁脚)
CK PEG3.05 (前脚3.05) 2-BACK PEG3.85 (后脚3.85)
PEG (后背铁脚) :0-W/O BACK PEG (无后背铁脚)
ACK PEG (1个后背铁脚) 2-BACK PEG (2个后背铁脚)
ACK PEG (3个后背铁脚)
LD MATERIAL STYLE (屏蔽壳材料分类) :
*PER ALLOY (黄铜) ;2-STEEL ALLOY (铜片) ;3-W/O (不作定义)
STYLE: (LED 颜色类型) :0-W/O LED (不带灯)



MM (INCH)		设计 ZHANG WEI	日期 14.03.10	浙江创都电子科技有限公司	
一 般 公 差 表		审核	日期		
MM	±	批准 ZHANG KE	日期 14.03.10	系列	名称 RJ5224-8P8C-C-GY-L
.0 ±0.30	±	材料: 材料	数量: 数量	系列	
.00 ±0.25	±	表面处理: 表面处理	图号: J	图号: 1111121	A3 版本
.000 ±0.1	±	比例: 比例	不按比例	关 X 页	第 Y 页
角度 ± 0.01°					
第三角视图					