




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		电路图修正，图面升级整理图面	2025.07.25	阿树

A



B

C


D



电路图：常开式 (N.O)
1个电路1个接点
端子排列 (自A方向看)



PCB LAYOUT



⑤	Contact Spring	1	Phosphor Bronze	CU/EP Ni Ag
④	Terminal	3	Brass	Black
③	Base	1	PPA	CU/EP Ni Ag
②	Cover	1	PPA	Black
①	Keystake	1	PPA	Black
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

DESIGN	阿树	VIEW:				MODEL TYPE: DETECT SWITCH
CHECKED		UNIT: mm/in	PART NO.: TM-1630-B			
APPROVED		SIZE: A4	DWG NO.:			
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1/1	REVISION A1	

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED