



1 2 3 4 5 6 7 8 9 10 11




技术参数 (SPECIFICATION):

温度范围 (TEMPERATURE RANGE): -40~+70 °C
 额定电压 (VOLTAGE RATING): 125V
 额定电流 (CURRENT RATING): 1.5A
 接触电阻 (CONTACT RESISTANCE): ≤30mΩ
 绝缘电阻 (INSULATION RESISTANCE): ≥500MΩ
 耐压 (DIELECTRIC STRENGTH): 1000V AC/(50HZ)/Min
 插拔力 (MATING AND UNMATING FORCE): 3~20N
 寿命 (DURABILITY): 750 CYCLES MIN

材料 (MATERIAL):

基座 (HOUSING): PBT UL94V-0
 插针 (CONTACT): PHOSPHOR BRONZE \varnothing 0.46mm
 镀层 (PLATING): GOLD PLATING OVER NICKEL
 外壳 (SHIELD): COPPER ALLOY $t=0.2$ mm PLATING NICKEL



PCB LAYOUT (TOP VIEW)
RECOMMENDED

网络插座外形图

浙江创都电子科技有限公司

绘图:

品名:

网络插座

日期:

料号:

RJ59-01YG-WT3.05

审核:

日期:

型号:

RJ45

图号:

核准:

角度:

版本:

1 of 1

页数:

单位:mm

比例: 1:1

纸张: A4

A/0	出版发行			变更单号	绘 制	日 期			
版次	变更履历			核 准:	日 期:				
1				1 of 1					
1				单位:mm					