








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A)X6	产品外观及尺寸变更，图面升级整理图面	2025.07.19	阿树



SCHEMATIC	
Model	DC-005-5.0A
Center Pin	Ø2.0 mm Ø2.5 mm



⑥	Housing	1	PA(Black)	
⑤	Cover	1	PA(Black)	
④	PIN	1	H65 Ø2.0	CuSn-Plated
③	Terminal 3#	1	Brass T=0.30	Ag-Plated
②	Terminal 2#	1	Phosphor Bronze T=0.30	Ag-Plated
①	Terminal 1#	1	Brass T=0.40	Ag-Plated
NO.	PART NAME	QTY	MATERIAL(Thick,color)	REMARK

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	DC POWER JACK
PART NO.:	DC-005-5A-2.5-SMT
DWG NO.:	