








SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating:250V AC, DC
- 3、Temperatuer Range:-25℃~+85℃
- 4、Contact Resistance:20mΩ Max
- 5、Insulation Resistance:1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:
Wafer: LCP, UL94V-0
PIN: Brass Tin-plated
Solder Phosphoric bronze Tin-plated

Poles	PART NO.	Dimension mm	
		A	B
2	W-2004N02P-B400	2.00	8.00
3	W-2004N03P-B400	4.00	10.00
4	W-2004N04P-B400	6.00	12.00
5	W-2004N05P-B400	8.00	14.00
6	W-2004N06P-B400	10.00	16.00
7	W-2004N07P-B400	12.00	18.00
8	W-2004N08P-B400	14.00	20.00
9	W-2004N09P-B400	16.00	22.00
10	W-2004N10P-B400	18.00	24.00
11	W-2004N11P-B400	20.00	26.00
12	W-2004N12P-B400	22.00	28.00
13	W-2004N13P-B400	24.00	30.00
14	W-2004N14P-B400	26.00	32.00
15	W-2004N15P-B400	28.00	34.00

APPROVED:	DATE:	C 深圳市灿科盟实业有限公司 kmtw CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:·	DATE:	TITLE: 2001SMT-XP 立贴 带扣			
DRAWN: LYF	DATE: 2018-05-28	CLIENT P/N		W-2004NXXP-B400	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2001-0032	REV.	A JLX0

TOLERANCE TABLE	
. 0	±0. 20
. 00	±0. 10
. 000	±0. 05