

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	①X6	增加对插引导弧度管控, 修改尺寸, 图面升级整理图面	2025.07.09	阿树

Specifications:
规格:
Voltage rating:50V AC/DC
额定电压: 50V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:250V AC/minute
耐受电压: 250V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:≥100MΩ MIN
绝缘电阻: ≥100MΩ
Contact resistance:20mΩ MAX
接触电阻: ≤20mΩ
Applicable wire Range:AWG#28-#32
使用线范围: AWG #28-#32

PART NO.:
X1004 T-P XX-A
① ② ③ ④ ⑤

- ①Series Number.
②Category: T-terminal
③Material:P-Phosphor bronze
④Plating Style: V01-All Gold Flash
SN-Bright tin Plating 80u";
120u" Over Nickel
⑤Type: Type A

X1004T-PXX-A	Phosephor Bronze	X1004T-L	X1004H-L
PART NO	Material	Suitable SWB Terminal	SuitableXKB Housing

MODEL TYPE: 2.54mm Crimp Style Connector	VIEW:	PART NO.: X1004T-PXX-A
DWG NO.:	UNIT: mm/in	SIZE: A4
SCALE N/A	PAGE 1/1	REVISION A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

