

1 2 3 4 5 6 7 8 9 10 11

A B C D E 改善意见  
止在图面上

**技术参数 (SPECIFICATION):**

- 温度范围 (TEMPERATURE RANGE): -40~+70°C
- 额定电压 (VOLTAGE RATING): 125V
- 额定电流 (CURRENT RATING): 1.5A
- 接触电阻 (CONTACT RESISTANCE): ≤30mΩ
- 绝缘电阻 (INSULATION RESISTANCE): ≥500MΩ
- 耐压 (DIELECTRIC STRENGTH): 500V AC/(50Hz)/Min
- 插拔力 (MATING AND UNMATING FORCE): 3~20N
- 寿命 (DURABILITY): 750 CYCLES MIN

**Table 1**

X	Terminal Plating
0	Au "Fu" Plating
1	Au "1u" Plating
2	Au "2u" Plating
3	Au "3u" Plating
4	Au "6u" Plating
5	Au "10u" Plating
6	Au "15u" Plating
7	Au "30u" Plating

**Material & Plating**

Part NO.: RCH563114-DW-X-XX

LED position

**Table 2**

D	L LED/R LED
YG	YELLOW/GREEN
GY	GREEN/YELLOW
YY	YELLOW/YELLOW
GG	GREEN/GREEN
OO	OTHER/OTHER

**Table 3**

XX	Material/Color
BB	PBT/BLACK
BW	PBT/WHITE
AB	PA/BLACK
AW	PA/WHITE
OO	OTHER/OTHER

**网络插座外形图**

绘图: 日期:

审核: 日期:

核准: 日期:

A/0 新出版发行

版次 变更履历 变更单号 绘制 日期 核准 日期

浙江创都电子科技有限公司

RJ56-31-14DL-WT

一 般 公 差

30~	±0.25	品 名:		
10~30	±0.20	料 号:		
~10	±0.15	型 号:	RJ45	图 号:
角 度:	±2°	页 面:	1 of 1	版 本:
				单 位:mm 比 例:1:1 纸 张:A4