



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A (A1)X4		产品尺寸变更, 图面升级整理图面	2025.08.12	阿树






SS-12D10 X X X

Knob Type
L
G


H(mm)
2~12

Colour
Blank:Standard Black
R:Red



Specifications(规格):

- 1.Rating(额定值):1A 250V AC
- 2.Contact resistance(接触电阻):≤30mΩ
- 3.Insulation resistance(绝缘电阻):≥100MΩ
- 4.Mating cycles (使用寿命): ≥10000 cycles
- 5.Operation force (操作力): 250±100gf
- 6.Temperature range(使用温度):-30℃~+85℃



7	Terminal	3	Brass	Ag-plated
6	Needle holder	1	PA66	Red
5	Contact Sheet	1	Brass	Ag-plated
4	Ball	1	carbon steel	Ag-plated
3	Shell	1	SUS	
2	Spring	1	carbon steel	
1	Slide Handle	1	PA66	Black
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING/COLOR

Function		
ON	NA	ON
● ○	/	○ ●

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	SLIDE SWITCH
APPROVED		SIZE: A4	PART NO.: SS-12D10xxx
			DWG NO.:
		SCALE	PAGE
		N/A	1/1
		REVISION	A1